
ASCO™ MINIATURE SOLENOID VALVES

GENERAL SERVICE VALVES, 3-WAY UNIVERSAL

SERIES 226

- The Series 226 3-way direct acting solenoid valve can be used with both liquids and gases
- Low power consumption, as well as latching coil versions, results in a decrease in OEM instrument power consumption as well as a decrease in heat transferred to the fluid media
- Small form-factor saves space in OEM instruments and are well-suited for portable and hand-held field devices
- Multiple electrical connection options offer greater flexibility in OEM instrument design and serviceability
- Meets all relevant CE directives, and is RoHS compliant
- Typical applications include:
 - Dental Equipment
 - Gas Chromatography
 - _ Industrial Analyzers
 - Respiratory Devices






Fluids*	Temperature Range	Seal Materials*			
Liquids and gases	-10°C to 90°C (14°F to 194°F) (NBR) 0°C to 90°C (32°F to 194°F) (FKM)	NBR or FKM			

Ensure that the compatibility of the materials in contact with the fluids is verified.

General Valve Information							
Body	Brass						
Internal components	Brass, PEI (Polyetherimide) and stainless steel						
Seat	$1 \leftrightarrow 2$: Brass - 1 \leftrightarrow 3: PEI						
Core tube	Brass						
Maximum allowable pressure (PS)	16 bar (232 psi)						
Response Time	<10ms						
Max viscosity	3°E (22 cStokes or mm²/s)						



Electrical Characteristics						
Continuous duty	ED 100%					
Encapsulation material	PA (Polyamide) fiberglass reinforced					
Insulation class	F (155°C)					
Ambient temperature	-10°C to 60°C (14°F to 140°F)					
Electric connection*	DIN 46340 – micro plug connector					
Electrical Enclosure Protection	IP 65 (EN 60529) with micro plug connector					
Standard Voltages	DC: 12 VDC, 24 VDC (+10% - 5%)					

* leaded coil on request

NOTE:

Asco

BCAE

These micro-solenoid valves are not suitable for stagnating media subject to vaporization which deposit solid, calcareous, incrusting residues or similar. Sealings: NBR = Nitrile Butadiene Rubber FKM = Fluoro-carbon elastomer.

1 - For reference, F1 = 24 VDC; F3 = 12 VDC



Visit our website at emerson.com

Availability, design and specifications are subject to change without notice. All rights reserved.


青岛秉诚自动化设备有限公司 地址:中国·青岛市重庆南路99号海尔云街甲3号楼7F 服务热线:4006-918-365 网址:http://www.asco.store

ASCO™ MINIATURE SOLENOID VALVES

GENERAL SERVICE VALVES, 3-WAY UNIVERSAL

Specifications															
Port size ISO UNI 4534	Orifice Size mm (inches)	Operating Pressure, bar (psi)						Damas Alas anatian					Malhawa		
		Δp min		Δp max			Kv (m ³ /h)	Cv	Power Absorption			Seclingo	Catalog Number	Voltage	
			Gases		Liquids				AC (VA)		DC	Sealings	Catalog Nulliber	12V	24V
			AC	DC	AC	DC]		Inrush	Holding	(W)			DC	DC
M5	1.2 (0.047)	0	D -	6 (87)		6 (87)	0.04	0.05			2.5	NBR	H226A556S0A00	F3	F1
				8 (116)		8 (116)					4 2.5		H226A557S0A00	F3	F1
				6 (87)	1	6 (87)							H226A559S0A00	-	F1
				8 (116)]	8 (116)				-	4		H226A560S0A00	-	F1
	2 (0.079)			6 (87)	-	6 (87)			-				H226A566S0A00	-	F1
				6 (87)]	6 (87)					4	FKM	H226A562S0A00	-	F1
				2.5 (36)		2.5 (36)		0.09				NBR	H226A558S0A00	-	F1
				1.5 (22)]	1.5 (22)							H226A567S0A00	F3	-
				1.5 (22)		1.5 (22)						FKM	H226A563S0A00	F3	-

Dimensions: mm (inches)



Installation

Solenoid valve can be mounted in any position; vertical with coil upwards preferred.

NOTE:

It is necessary to keep the current circulating in the coil constant, so as to maintain the solenoid valve in any pre-determined position. In case the solenoid valve is energised by voltage variation, it has to be considered that the resistance of winding increases because of the continued energizing and consequently the power decreases. Therefore, it is necessary to compensate such power decrease by increasing the voltage to re-establish the initial current value.





Visit our website at emerson.com

Availability, design and specifications are subject to change without notice. All rights reserved.

青岛秉诚自动化设备有限公司 地址:中国·青岛市重庆南路99号海尔云街甲3号楼7F 服务热线:4006-918-365 网址:http://www.asco.store Asco

传真:(86-532)585-10-365 Email:sales@bechinas.com